

Quality

The new CONCEPT WVModular dryers are an example of modern engineering technology, giving the user a value for money installation. It has the highest quality with built-in reliability at the lowest running costs.

The ZANDER CONCEPT WVM_{odular} adsorption dryer range is the synonym for:

- 1 Low Energy Costs**
savings of 25% are possible compared to conventional systems.
- 2 Two layered desiccant bed**
balanced desiccant between water resistance and high efficiency water retention for optimum dew point stability.
- 3 Active heating under vacuum**
means that the vaporization temperature is 98°C.
- 4 Low regeneration temperature**
for the desiccant bed compared to conventional systems.
- 5 Intensive cooling**
using the vacuum without any heat generation from the vacuum pump.
- 6 Regeneration without purge air**
thanks to the high temperature difference even after the cooling phase.
- 7 Pressure build up on the wet side**
guarantees no purge air even on the pressure build up phase.
- 8 Reliable dew point**
as the regeneration air flows through the dryer inlet in the same direction as the air to be dried.
- 9 Changeover without dew point peak**
the moisture entering the desiccant bed during the regeneration and cooling phase never reaches the drying zone.
- 10 Reliable dew point down to -70°C**
standard dew point available at -25°C and -40°C.
- 11 New function alarm**
for pressure, inlet temperature, heating, vacuum pump and vessel changeover.
- 12 Alternative energies**
available for regeneration as an optional extra: steam, hot water. Please consult ZANDER for other heat sources.
- 13 Modular system options**
* controlled regeneration air
* thyristor controlled heating
* variable speed vacuum pump motor.

Technical Data

Type concept	Capacity (m ³ /h)*	Connect. DN	Width (mm)	Height (mm)	Depth (mm)	Weight kg	Electr. connect kWh/h
WVM 40	420	40	1215	1955	992	460	3,1
WVM 50	510	40	1215	2205	992	560	3,8
WVM 65	640	50	1305	2250	1085	750	5,2
WVM 85	850	50	1360	2275	1120	800	6,7
WVM 120	1180	80	1560	2665	1265	1150	10,9
WVM 150	1500	80	1610	2680	1265	1350	12,8
WVM 200	1980	80	1700	2730	1595	1720	16,3
WVM 235	2350	100	2020	2845	1450	1880	18,1
WVM 300	2930	100	2090	2870	1580	2350	22,5
WVM 355	3550	100	2170	2940	1740	2850	27,9
WVM 410	4100	150	2450	3190	1780	4000	32,5
WVM 475	4740	150	2550	3210	2110	4100	38,9
WVM 525	5250	150	2550	3230	1955	4200	44,8
WVM 620	6210	150	2600	3500	1910	4950	52,3
WVM 710	7100	150	2650	3520	1940	5700	56,3
WVM 800	8000	200	3100	3585	2180	6400	67,2
WVM 920	9200	200	3150	3605	2300	7400	75,6
WVM 1080	10800	200	3250	3670	2355	8700	85,3
WVM 1230	12300	250	3500	3855	2515	11500	98,9
WVM 1450	14500	250	3600	3895	2570	13500	111,4

*m³/h calculated at 1 bar according to DIN 7183

Examples of calculation:

a) Compressed air to be treated
Flow 3000 m³/h
Pressure 5 bar (ü)
Maximum inlet temp. + 30°C
Dew-point - 25°C
Factor P from table 0,80

$$\frac{\text{flow}}{\text{conversion factor}} = \frac{3000 \text{ m}^3/\text{h}}{0,80} = 3750 \text{ m}^3/\text{h}$$

Choose Type concept WVM 410


b) Calculation of maximum flow
flow x conversion factor
4100 x 0,80 = 3280 m³/h

c) Reserve available equals
maximum flow - actual flow
3280 m³/h - 3000 m³/h = 280 m³/h

Higher flows and dew-point to -70°C on request


Factors for calculating size of dryer at temperature flows and pressure.

bar(ü) \ °C	30	35	40
4	0,69	0,44	0,28
5	0,80	0,62	0,42
6	0,90	0,80	0,59
7	1,02	1,00	0,70
8	1,06	1,05	0,79
9	1,17	1,16	0,88
10	1,29	1,28	0,96



We reserve the right to change design and dimensions.

Adsorption Dryer



CONCEPT
WVM_{odular}



ZANDER Aufbereitungstechnik GmbH
Im Teelbruch 118, D-45219 Essen
Postfach 18 55 24, D-45205 Essen
Tel. (0 20 54) 9 34-0 · Telefax (0 20 54) 9 34-164
Internet: <http://www.zander.de>
A Division of Parker Hannifin Corporation

ZANDER® The CONCEPT WVM_{odular} Adsorption Dryer

The new generation...

of ZANDER patented vacuum heat regenerated adsorption dryers is the result of continuous research and development based on years of experience with user installations worldwide.

The name ZANDER is synonymous with the best in compressed air treatment. The new CONCEPT WVM_{odular} range adds to the reputation with optimum efficiency and reliable and constant high quality. This level of quality is reflected in the pressure dew

point, which can be both measured and proved. The designated pressure dew point of a CONCEPT WVM_{odular} dryers remains continuously constant, so important in today's systems. The constant dew point is achieved by using two layers of desiccant and regeneration under vacuum. This ZANDER vacuum regeneration with Active Heating and Intensive Cooling defines the new standard for heat regenerated dryers.

Adsorption

Desiccant attracts and stores the moisture from the saturated compressed air. ZANDER'S experience over many years designing and building heat regenerated dryers has resulted

in the ideal ratio of high capacity and long life medium. The most economical form of desiccant bed is to combine the correct proportions of water resistant with high efficiency desiccant. The


Regeneration

Using the vacuum technology with low regeneration temperatures and the economical ratio of

desiccant results in optimum efficiency and stable long term dew point.




filling of desiccant in the new dryers means low energy costs. A longer service life and a steady dew-point.



Active Heating

The ZANDER vacuum system reduces the regeneration pressure. Only heating under vacuum guarantees the greatest desiccant activation. Regeneration

under vacuum also means a lower steam vapour temperature. Active heating results in less energy requirement and the benefit of less cooling.



Intensive Cooling

Cooling air flows in the same direction as the dried compressed air. This prevents moisture loading at the outlet of the dryer. The advantages of this system are lower temperatures; shorter

cooling times; lower energy requirements; a lower water loading; a short cooling time and no expensive compressed air required for cooling.



Digital Control

The user friendly digital control installed on the CONCEPT WVM_{odular} dryers ensures a reliable operation of the unit. The ZANDER units have a perfect set of system relevant signals. These signals define and control the active heating and active cooling phases in the regeneration cycle within very exact tolerances. The result of these fine tolerances is

that the dryer adapts exactly to the working pattern in the plant, thus the new dryer only uses the energy required for its working conditions. In addition, the user has a complete picture of the operation of the dryer through the display flow sheet. The user can take information about the dryer's performance to a BMS system.

